Industrial Portable UV Sanitation Cart - Kills 99% of Viruses - 8000 sq. ft. Area - 304 Stainless Steel - 50' Cord - Digital Timer

IND-UC.360-48-8L-UVC-V3-AT-KT-50C



This unit is Made In USA - Manufactured in Texas

IND-UC.360-48-8L-UVC-V3-AT-KT-50C UV Sanitation Light Cart

Lamp Technology: UV-C Fluorescent

Lamp Qty: (8)

Dimensions:19"-W x 19"-D x 68"-H

Weight: 100 lb

Voltage: 120V AC, 50/60Hz

Total Watts: 960W Single-lamp Watts: 120W Total UV Output: 212.8W Single-lamp UV Output: 26.6W Expected Lifespan: 8,000+ Hours

UV Wavelength: UV-C, 200nm - 280nm (254 nm)

Lamp Type: T8HO Lamp Base: G13

Replacement Lamp: FRL-48-1X-T8HO-120W-UV-C

Beam Angle: 360° Light Configuration: Flood

Delay: 1 Minute and 30 Seconds at Startup Maximum Treatment Time: 24 Hours Safety Kit: (2) Safety Goggles, (4) Safety Signs

Ambient Operating Temp: 80°F Materials: 304 Stainless Steel

Lamp Protection: Wire Guard and Center Rail

Mounting: Portable - (4) Wheels

Wiring: 50' 16/3 SOOW Cord w/ Cord Cap Cord Cap: 5-15 Straight, L5-15 Twist, or Pigtail

PLEASE NOTE: UV-C light can cause temporary or permanent loss of vision, and temporary acute redness or ulceration (mild to severe sunburn) to exposed skin. To prevent exposure, do not operate the device in any application that allows UV-C light to be visible during operation. NEVER LOOK DIRECTLY AT THE BULB OR DISINFECTING TARGET ZONE. DO NOT touch bulb with bare hands. The oils in your skin will damage the lamp. Fingerprints will result in reduced performance and significantly reduce the lifespan of the lamp unless they are removed with alcohol. Please read instruction manual for UV safety requirements before operating.

Ratings/Features

Short-wave Germicidal Light Kills 99% of Viruses and Other Germs Cooling Fans Safety Kit Included

Special Orders - Requirements

Contact us for special requirements

Toll Free: 1-800-369-6671 Intl: 1-214-616-6180

Fax: 1-903-498-3364

E-mail: sales@larsonelectronics.com

This unit is Made In USA - Manufactured in Texas

The Larson Electronics IND-UC.360-48-8L-UVC-V3-AT-KT-50C is an Industrial Portable UV Sanitation Cart which can kill 99% of viruses, bacteria, mold, and spores in large facilities. This unit offers UV-C output at a range of 200nm - 280nm (254nm) and comes equipped with eight UVC fluorescent lamps. Capable of disinfecting an entire room, the 304 Stainless Steel UV system comes with 50' of 16/3 SOOW cord and a safety kit (two goggles and four safety signs).

Please note: This product produces UV light. Make sure to follow all safety guidelines and protocols found in the user manual. UVC light in the proper setting kills up to 99.9% of viruses, mold, spores and bacteria. Click here to learn more about UVC and the corona virus

The IND-UC.360-48-8L-UVC-V3-AT-KT-50C is a powerful sanitation solution for industrial sites and commercial facilities. Equipped with eight UVC fluorescent lamps, this system offers output within the 200nm - 280nm UV-C range (254 nm). The lights have an expected lifespan of 8,000+ hours and emits a flood beam pattern. This UV system caters to 8,000 square feet of space with full, 360 degrees of coverage. Cooling fans below the lamps keep the unit running optimally. There is a delay of 1 minute and 30 seconds at startup for clearing the area after activation. Operators may move the cart around after exposure time to disinfect several sections.

Distance from Cart	Irradiance/Second	Exposure Time Required*	Beam Width	Beam Height
6 inch	4829.76 uW/cm2	8.7 seconds	2 ft	4 ft
12 inch	2426.11 uW/cm2	17.31 seconds	2.25 ft	4 ft
18 inch	1347.84 uW/cm2	31.16 seconds	2.5 ft	4 ft
2 foot	872.35 uW/cm2	48.15 seconds	3 ft	4 ft
3 foot	456.77 uW/cm2	1.5 minutes	4.5 ft	4 ft
4 foot	230.26 uW/cm2	3 minutes	6 ft	4 ft
5 foot	147.36 uW/cm2	4.75 minutes	7.5 ft	4 ft
6 foot	102.34 uW/cm2	7 minutes	9 ft	4 ft
7 foot	75.19 uW/cm2	9.5 minutes	10.5 ft	4 ft
8 foot	57.56 uW/cm2	12.5 minutes	12.25 ft	4 ft
9 foot	45.48 uW/cm2	16 minutes	13.5 ft	4 ft
10 foot	36.84 uW/cm2	19 minutes	15.25 ft	4 ft
12 foot	25.58 uW/cm2	28 minutes	18.5 ft	4 ft
15 foot	16.37 uW/cm2	43 minutes	23 ft	4 ft
18 foot	11.37 uW/cm2	62 minutes	27.5 ft	4 ft
20 foot	9.21 uW/cm2	76 minutes	30 ft	4 ft

^{*}Exposure time is based off of total irradiance. The above calculations are based on 12mJ total exposure. This level of exposure deactivates most organisms.

This unit is made out of 304 Stainless Steel and features spring-loaded lamp sockets, which makes it easier to switch out lamps. A wire guard protects the UV lamps from tampering or accidental bumping. Two safety goggles (not full face masks) and four safety signs (to warn individuals about ongoing UV sanitation) are included with the light. With a recommended 20-25 minute exposure time for viruses, multiple carts can be purchased to cover larger areas quicker. The UV light can disinfect over 99% of bacteria, viruses, mold, and spores.

Click Photos to Enlarge 5-15 Straight Blade Plug

5-15 Straight Blade Plug L5-15 Twist Lock Plug 15 Amp / 125V Rated 15 Amp / 125V Rated

Flying Leads / Pigtail Wires

Wiring/Plug: This unit is equipped with 50 feet of 16/3 chemical and abrasion resistant SOOW cord that is fitted with an industrial grade cord cap for easy connection to common wall outlets. Plug options include standard 5-15 15 amp straight blade plug for 110V wall outlets with ground or NEMA L5-15 15 amp twist lock plug for 125V twist lock outlets. Alternatively, we can provide flying leads with no plug for hard wire applications or for operators who prefer to wire in user provided cord caps. Please choose pigtail option below for flying leads with no



plug.

Cart: Operators can easily move the UV lighting system around facilities via four wheels at the bottom. A center rail enables seamless guidance and positioning of the unit. For best results, the light should be setup in the middle of the area. **Note on Environment:** Sunlight and visible light fixtures do not impact the effectiveness of the disinfecting on this UVC sanitation product. Metal halide, high pressure sodium, fluorescent, and LED light fixtures can be left on. The UV radiation emitted from this product is not disrupted by any type of lighting in the environment. Put simply, NO it DOES NOT need to be dark in the area you plan to disinfect. The UV radiation is harmful to the eyes and skin, and that is why you should not be in the area while it is in operation. Please see user manual for additional safety information.

Suggested Applications: Sanitation, disinfection, killing 99% of viruses, bacteria, mold, and spores, retail spaces, lobbies, commercial locations, industrial parks, schools, public transportation hubs, airports, office buildings, medical centers and more.

At Larson Electronics, we do more than meet your lighting needs. We also provide replacement, retrofit, and upgrade parts as well as industrial grade power accessories. Our craftsmen can custom build any lighting system and/or accessories to fit the unique demands of your operation. A commitment to honesty, quality, and dependability has made Larson Electronics a leader in the lighting and electronics business since 1973. Contact us today at 800-369-6671 or message sales@larsonelectronics.com for more information about our custom options tailored to meet your specific industry needs.

Frequently Asked Questions (FAQ)

Q. How long does the fixture need to operate to kill viruses?

A. 30 minute exposure time is required for killing viruses

Q. What if I want to disinfect a larger area than the square footage that is listed in the specifications of this product?

A. You can move the product and cover other areas. Each time the unit is moved, the exposure time starts again.

Q. What if obstacles are in the way of the UV light while it is disinfecting?

A. You will need to move objects around and disinfect again for another 30 minutes. If the cart does not have direct line of sight, it will not disinfect. This is a non-ozone UV generating product so it does not penetrate through solid surfaces and will not reflect and clean the underside of objects or behind objects. If you do not have direct line of sight from the light, you will need to move it around or move the obstacles to create proper exposure.

Q. Does this product come with UV lamps

A. Yes. This product will ship with UV lamps. The required UV lamps are included with your purchase.

Q. Is this unit safe to use in occupied areas?

A. No. This unit produces UV radiation. UV radiation is NOT safe for your skin or eyes. Please read manual for UV safety requirements.

Q. Do I need to wear protective gear?

A. Yes. UV radiation is NOT safe for your skin or eyes. Please read manual for UV safety requirements.

Q. Is this product skin safe or eye safe?

A. No. UV radiation is not safe for the eyes or skin. Please read manual for UV safety requirements.

Q. Does this product generate ozone?

A. No. UV lights can be made as ozone-producing or non-ozone producing. Ozone producing lamps leaves radiation in the atmosphere and require a 20-30 minute time after lamps are turned off before the radiation levels dissipate to a safe level before you can re-enter the room/area. The products that Larson Electronics manufactures DO NOT use ozone-producing lamps. This means that the radiation stops the second the light turns off. Once the light is turned off, it is safe to return to the area being disinfected by the light. Please read manual for UV safety requirements.

Q. Does this product kill he SARS-CoV-2 coronavirus?

A. Please see below link for effectiveness against viruses, including the 2019 SARS-CoV-2 coronavirus: https://www.larsonelectronics.com/images/product/LightingFacts/266985.PDF

Q. Does this product kill COVID-19?


A. COVID-19 is the disease created from the SARS-CoV-2 coronavirus. Please see below link for effectiveness against viruses, including the 2019 SARS-CoV-2 coronavirus:

https://www.larsonelectronics.com/images/product/LightingFacts/266985.PDF











Options:

IND-UC.360-48-8L-UVC-V3-AT-KT-50C-Cord Cap Example: IND-UC.360-48-8L-UVC-V3-AT-KT-50C-5.15

Cord Cap				
5-15 STRAIGHT	-5.15			
L5-15 TWIST	-L5.15			
PIGTAIL	-Pigtail			

Links (Click on the below items to view):

- addpic1large
- addpic2large
- addpic3large
- addpic4large
- BeamInfo
- CatalogPage
- large
- LightingFacts
- Manual
- medium
- MSDS
- SpectrumChart
- WiringDiagram
- HigResPic1
- HigResPic2
- HigResPic3
- HigResPic4
- HigResPic5
- HigResPic6
- HigResPic7
- Video1
- Video2
- Video3
- Video4
- CECCert
- Cert1
- EyeSafety
- NECCert